




MONITOR 22" x 2 OFF




PC TOWER


EXTERNAL POWER BOX
WALL MOUNTED ENCLOSURE




DEWAR TANK
(CRYO OPTION)




LN2 CHANGE-OVER BOX
(CRYO OPTION)




ANCILLARY ITEMS



FP51 CHILLER



ACP15G LOAD-LOCK PUMP



A124H CHAMBER PUMP

NOTES
PLEASE NOTE OPT RECOMMENDS THE APPLICATIONS OF BS EN (IEC) 60204-33 REQUIREMENTS OF ONE METRE ACCESS TO MAINTENANCE POINTS AROUND THE TOOL WHERE ELECTRICAL EQUIPMENT IS LIKELY TO BE LIVE DURING ACCESS AND ENERGISED PARTS ARE EXPOSED WHEN ENCLOSURE IS OPEN.

SEE BOM		PLASMA TECHNOLOGY	
94-CL-1960011	01	CL-ESTRELAS-LI-ICP-INTER	94-CL-1960011 01
PLASMA TECHNOLOGY	1276.86 kg	AG	SHEET 1 OF 2

